

Clamping piece with extension

SXT-CL-EXT-A2-175-F25



Art.-Nr.: 10.07.13.00077




Technical data

Attribute	Value
Material	Aluminum
Outside diameter D	25.00 mm
Internal diameter d	19.00 mm
Connection 1	Bolt with slot Ø19mm
Hole spacing X1	176.0 mm

SXT-CL-EXT-A2-175-F25

Clamps with extension SXT-CL-EXT are delivered as a ready-to-connect product.



Design data

Attribute	Value
Length L1	223.50 mm
Length L2	125.00 mm
Length L	215.50 mm
Width B	25.00 mm
Height H1	71.00 mm
Height H2	19.50 mm
Outside diameter D	25.00 mm
Internal diameter d	19.00 mm
Height H3	12.50 mm
Hole spacing X1	176.0 mm

Design data SXT-CL-EXT-A2-175-F25



WWW.SCHMALZ.COM/10.07.13.00077

Clamping piece with extension

SXT-CL-EXT-A2-175-F25



Art.-Nr.: 10.07.13.00077



Technical data

Attribute	Value
Weight	375.00 g
Material	Aluminum
Product family	SXT
Shape	Female



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.07.13.00077



WWW.SCHMALZ.COM/10.07.13.00077