

Clamping piece with extension

SXT-CL-EXT-A2-125-F40



Art.-Nr.: 10.07.13.00082




Technical data

Attribute	Value
Material	Aluminum
Outside diameter D	40.00 mm
Internal diameter d	19.00 mm
Connection 1	Bolt with slot Ø19mm
Hole spacing X1	126.0 mm

SXT-CL-EXT-A2-125-F40

Clamps with extension SXT-CL-EXT are delivered as a ready-to-connect product.



Design data

Attribute	Value
Length L1	179.50 mm
Length L2	75.00 mm
Length L	171.50 mm
Width B	25.00 mm
Height H1	83.00 mm
Height H2	25.50 mm
Outside diameter D	40.00 mm
Internal diameter d	19.00 mm
Height H3	12.50 mm
Hole spacing X1	126.0 mm

Design data SXT-CL-EXT-A2-125-F40



WWW.SCHMALZ.COM/10.07.13.00082

Clamping piece with extension

SXT-CL-EXT-A2-125-F40



Art.-Nr.: 10.07.13.00082



Technical data

Attribute	Value
Weight	320.00 g
Material	Aluminum
Product family	SXT
Shape	Female



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.07.13.00082



WWW.SCHMALZ.COM/10.07.13.00082