


Art.-Nr.: 10.07.13.00234

**Technical data**

Attribute	Value
Material	Aluminum
Outside diameter D	25.00 mm
Internal diameter d	40.00 mm
Connection 1	D40
Length L3	200.50 mm

SXT-CL-EXT-D40-200-T25

Clamps with extension SXT-CL-EXT are delivered as a ready-to-connect product.

**Design data**

Attribute	Value
Length L1	228.00 mm
Length L2	175.00 mm
Length L	227.50 mm
Width B	25.00 mm
Height H2	25.50 mm
Height H	65.00 mm
Outside diameter D	25.00 mm
Internal diameter d	40.00 mm
Length L3	200.50 mm


Design data SXT-CL-EXT-D40-200-T25



Art.-Nr.: 10.07.13.00234

**Technical data**

Attribute	Value
Weight	250.00 g
Material	Aluminum
Product family	SXT
Shape	Tube

**Performance data**

Deflection pipe 25 x 3 mm

**Deflection pipe 25 x 3 mm**

	0	200	400	600
1 kg SXT-CL-EXT....T25	-	0.03	0.24	0.81
2 kg SXT-CL-EXT....T25	-	0.06	0.48	1.61
5 kg SXT-CL-EXT....T25	-	0.15	1.20	4.03
10 kg SXT-CL-EXT....T25	-	0.30	2.39	8.07

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.07.13.00234WWW.SCHMALZ.COM/10.07.13.00234