

Clamping piece with extension SXT-CL-EXT-A3-110-T25



Art.-Nr.: 10.07.13.00239




Technical data

| | |
|---------------------|-------------------|
| Material | Aluminum |
| Outside diameter D | 25.00 mm |
| Internal diameter d | 28.50 mm |
| Connection 1 | Ball head 28.5 mm |
| Length L3 | 110.10 mm |

SXT-CL-EXT-A3-110-T25

Clamps with extension SXT-CL-EXT are delivered as a ready-to-connect product.



Design data

| | |
|---------------------|-----------|
| Length L2 | 75.00 mm |
| Length L | 137.10 mm |
| Width B | 25.00 mm |
| Height H2 | 23.50 mm |
| Height H | 57.00 mm |
| Outside diameter D | 25.00 mm |
| Internal diameter d | 28.50 mm |
| Length L3 | 110.10 mm |

Design data SXT-CL-EXT-A3-110-T25



Technical data

| | |
|----------------|----------|
| Weight | 250.00 g |
| Material | Aluminum |
| Product family | SXT |
| Shape | Tube |



WWW.SCHMALZ.COM/10.07.13.00239

1

Clamping piece with extension


SXT-CL-EXT-A3-110-T25



Art.-Nr.: 10.07.13.00239



Performance data



Deflection pipe 25 x 3 mm



Deflection pipe 25 x 3 mm

| | 0 | 200 | 400 | 600 |
|---------------------------|---|------|------|------|
| 1 kg SXT-CL-EXT....T25 | - | 0.03 | 0.24 | 0.81 |
| 2 kg SXT-CL-EXT....T25 | - | 0.06 | 0.48 | 1.61 |
| 5 kg SXT-CL-EXT....T25 | - | 0.15 | 1.20 | 4.03 |
| 10 kg SXT-CL-EXT....T25 | - | 0.30 | 2.39 | 8.07 |



WWW.SCHMALZ.COM/10.07.13.00239