

Clamping piece with extension

## SXT-CL-EXT-A5-310-T25



Art.-Nr.: 10.07.13.00250




### Technical data

| Attribute           | Value           |
|---------------------|-----------------|
| Material            | Aluminum        |
| Outside diameter D  | 25.00 mm        |
| Internal diameter d | 32.00 mm        |
| Connection 1        | Ball head 32 mm |
| Length L3           | 310.10 mm       |

SXT-CL-EXT-A5-310-T25

Clamps with extension SXT-CL-EXT are delivered as a ready-to-connect product.



### Design data

| Attribute           | Value     |
|---------------------|-----------|
| Length L2           | 275.00 mm |
| Length L            | 337.10 mm |
| Width B             | 25.00 mm  |
| Height H2           | 23.50 mm  |
| Height H            | 57.00 mm  |
| Outside diameter D  | 25.00 mm  |
| Internal diameter d | 32.00 mm  |
| Length L3           | 310.10 mm |

Design data SXT-CL-EXT-A5-310-T25



[WWW.SCHMALZ.COM/10.07.13.00250](http://WWW.SCHMALZ.COM/10.07.13.00250)

# Clamping piece with extension

## SXT-CL-EXT-A5-310-T25



Art.-Nr.: 10.07.13.00250




### Technical data

| Attribute      | Value    |
|----------------|----------|
| Weight         | 350.00 g |
| Material       | Aluminum |
| Product family | SXT      |
| Shape          | Tube     |



### Performance data



Deflection pipe 25 x 3 mm



### Deflection pipe 25 x 3 mm

|                           | 0 | 200  | 400  | 600  |
|---------------------------|---|------|------|------|
| 1 kg   SXT-CL-EXT....T25  | - | 0.03 | 0.24 | 0.81 |
| 2 kg   SXT-CL-EXT....T25  | - | 0.06 | 0.48 | 1.61 |
| 5 kg   SXT-CL-EXT....T25  | - | 0.15 | 1.20 | 4.03 |
| 10 kg   SXT-CL-EXT....T25 | - | 0.30 | 2.39 | 8.07 |



### Further documentation

CAD data and other documents relating to the article can be found at: [www.schmalz.com/10.07.13.00250](http://www.schmalz.com/10.07.13.00250)



[WWW.SCHMALZ.COM/10.07.13.00250](http://WWW.SCHMALZ.COM/10.07.13.00250)