

Plug union, straight

STVI-GE G1/8-IG 4



Art.-Nr.: 10.08.02.00149




Technical data

Attribute	Value
Material	Brass
Operating temperature	-20 ... 80 °C
Length L	23.50 mm
Outside diameter D	8.50 mm
Thread G1	G1/8"-F
Outer hose diameter	4.00 mm

STVI-GE G1/8-IG 4

The push-in fittings are supplied in the desired design.



Design data

Attribute	Value
Length L2	9.50 mm
Length L	23.50 mm
Outside diameter D	8.50 mm
Internal diameter d	4.00 mm
Thread G1	G1/8"-F
Thread length LG1	8.0 mm
Key width SW1	14.0 mm

Design data STVI-GE G1/8-IG 4



WWW.SCHMALZ.COM/10.08.02.00149

Plug union, straight

STVI-GE G1/8-IG 4



Art.-Nr.: 10.08.02.00149



Technical data

Attribute	Value
Weight	16.00 g
Material	Brass
Design hose type	4-2
Pressure range (operating pressure) [bar]	1.00 ... 15.00 bar
Operating temperature	-20 ... 80 °C
Product family	STV



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.08.02.00149



Ordering Data Accessories 10.08.02.00149

Typ		Item number
Compressed-air hose	VSL 4-2 PE BL	10.07.09.00013
Vacuum hose (meter)	VSL 4-2 PU MI-TR	10.07.09.00001
Vacuum hose (meter)	VSL 4-2.7 PA MI-TR	10.07.09.00063



WWW.SCHMALZ.COM/10.08.02.00149