

Plug union, straight

STVI-GE G1/8-IG 8



Art.-Nr.: 10.08.02.00151




Technical data

Attribute	Value
Material	Brass
Operating temperature	-20 ... 80 °C
Length L	29.50 mm
Outside diameter D	14.50 mm
Thread G1	G1/8"-F
Outer hose diameter	8.00 mm

STVI-GE G1/8-IG 8

The push-in fittings are supplied in the desired design.



Design data

Attribute	Value
Length L2	15.00 mm
Length L	29.50 mm
Outside diameter D	14.50 mm
Internal diameter d	8.00 mm
Thread G1	G1/8"-F
Thread length LG1	8.0 mm
Key width SW1	14.0 mm

Design data STVI-GE G1/8-IG 8



WWW.SCHMALZ.COM/10.08.02.00151

Plug union, straight

STVI-GE G1/8-IG 8



Art.-Nr.: 10.08.02.00151



Technical data

Attribute	Value
Weight	22.00 g
Material	Brass
Design hose type	8-6
Pressure range (operating pressure) [bar]	0.95 ... 15.00 bar
Operating temperature	-20 ... 80 °C
Product family	STV



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.08.02.00151



Ordering Data Accessories 10.08.02.00151

Typ		Item number
Compressed-air hose	VSL 8-6 PE BL	10.07.09.00015
Vacuum hose (meter)	VSL 8-6 PU MI-TR	10.07.09.00003



WWW.SCHMALZ.COM/10.08.02.00151