




STVI-GE G1/4-IG 6

The push-in fittings are supplied in the desired design.



Design data STVI-GE G1/4-IG 6

Technical data

Attribute	Value
Material	Brass
Operating temperature	-20 ... 80 °C
Length L	30.50 mm
Outside diameter D	11.50 mm
Thread G1	G1/4"-F
Outer hose diameter	6.00 mm

Design data

Attribute	Value
Length L2	12.00 mm
Length L	30.50 mm
Outside diameter D	11.50 mm
Internal diameter d	6.00 mm
Thread G1	G1/4"-F
Thread length LG1	12.0 mm
Key width SW1	17.0 mm

Plug union, straight

STVI-GE G1/4-IG 6



Art.-Nr.: 10.08.02.00153



Technical data

Attribute	Value
Weight	27.00 g
Material	Brass
Design hose type	6-4
Pressure range (operating pressure) [bar]	0.95 ... 15.00 bar
Operating temperature	-20 ... 80 °C
Product family	STV



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.08.02.00153



Ordering Data Accessories 10.08.02.00153

Typ		Item number
Compressed-air hose	VSL 6-4 PE BL	10.07.09.00014
Vacuum hose (meter)	VSL 6-4 PTFE MI-TR	10.07.09.00157
Vacuum hose (meter)	VSL 6-4 PU MI-TR	10.07.09.00002



WWW.SCHMALZ.COM/10.08.02.00153