

Plug union, elbow

STV-W M5-AG 4



Art.-Nr.: 10.08.02.00155




Technical data

Attribute	Value
Material	Nickel plated
Operating temperature	-20 ... 80 °C
Length L	16.40 mm
Thread G1	M5-M
Outer hose diameter	4.00 mm

STV-W M5-AG 4

The push-in fittings are supplied in the desired design.



Design data

Attribute	Value
Length L1	21.40 mm
Length L	16.40 mm
Height H1	13.60 mm
Height H	8.70 mm
Outside diameter D1	8.5 mm
Nominal diameter dn	2.50 mm
Internal diameter d	4.00 mm
Thread G1	M5-M
Thread length LG1	4.7 mm
Key width SW1	8.0 mm
Key width SW3	10.0 mm

Design data STV-W M5-AG 4



WWW.SCHMALZ.COM/10.08.02.00155

Art.-Nr.: 10.08.02.00155



Technical data

Attribute	Value
Weight	16.00 g
Material	Nickel plated
Design hose type	4-2
Pressure range (operating pressure) [bar]	-1.00 ... 15.00 bar
Operating temperature	-20 ... 80 °C
Product family	STV



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.08.02.00155



Ordering Data Accessories 10.08.02.00155

Typ		Item number
Compressed-air hose	VSL 4-2 PE BL	10.07.09.00013
Vacuum hose (meter)	VSL 4-2 PU MI-TR	10.07.09.00001
Vacuum hose (meter)	VSL 4-2.7 PA MI-TR	10.07.09.00063