

Plug union, elbow

STV-W G1/8-AG 6



Art.-Nr.: 10.08.02.00158




Technical data

Attribute	Value
Material	Nickel plated
Operating temperature	-20 ... 80 °C
Length L	20.10 mm
Thread G1	G1/8"-M
Outer hose diameter	6.00 mm

STV-W G1/8-AG 6

The push-in fittings are supplied in the desired design.



Design data STV-W G1/8-AG 6

Design data

Attribute	Value
Length L1	27.10 mm
Length L	20.10 mm
Height H1	19.90 mm
Height H	12.80 mm
Outside diameter D1	11.3 mm
Nominal diameter dn	4.10 mm
Internal diameter d	6.00 mm
Thread G1	G1/8"-M
Thread length LG1	5.7 mm
Key width SW1	13.0 mm
Key width SW3	14.0 mm



WWW.SCHMALZ.COM/10.08.02.00158

Plug union, elbow

STV-W G1/8-AG 6



Art.-Nr.: 10.08.02.00158



Technical data

Attribute	Value
Weight	30.00 g
Material	Nickel plated
Design hose type	6-4
Pressure range (operating pressure) [bar]	-0.95 ... 15.00 bar
Operating temperature	-20 ... 80 °C
Product family	STV



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.08.02.00158



Ordering Data Accessories 10.08.02.00158

Typ		Item number
Compressed-air hose	VSL 6-4 PE BL	10.07.09.00014
Vacuum hose (meter)	VSL 6-4 PTFE MI-TR	10.07.09.00157
Vacuum hose (meter)	VSL 6-4 PU MI-TR	10.07.09.00002



WWW.SCHMALZ.COM/10.08.02.00158