

Plug union, elbow

STV-W G1/4-AG 6



Art.-Nr.: 10.08.02.00159




Technical data

Attribute	Value
Material	Nickel plated
Operating temperature	-20 ... 80 °C
Length L	20.20 mm
Thread G1	G1/4"-M
Outer hose diameter	6.00 mm

STV-W G1/4-AG 6

The push-in fittings are supplied in the desired design.



Design data

Attribute	Value
Length L1	29.40 mm
Length L	20.20 mm
Height H1	20.40 mm
Height H	13.50 mm
Outside diameter D1	11.3 mm
Nominal diameter dn	4.10 mm
Internal diameter d	6.00 mm
Thread G1	G1/4"-M
Thread length LG1	7.5 mm
Key width SW1	17.0 mm
Key width SW3	14.0 mm

Design data STV-W G1/4-AG 6



WWW.SCHMALZ.COM/10.08.02.00159

Art.-Nr.: 10.08.02.00159



Technical data

Attribute	Value
Weight	37.00 g
Material	Nickel plated
Design hose type	6-4
Pressure range (operating pressure) [bar]	-0.95 ... 15.00 bar
Operating temperature	-20 ... 80 °C
Product family	STV



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.08.02.00159



Ordering Data Accessories 10.08.02.00159

Typ		Item number
Compressed-air hose	VSL 6-4 PE BL	10.07.09.00014
Vacuum hose (meter)	VSL 6-4 PTFE MI-TR	10.07.09.00157
Vacuum hose (meter)	VSL 6-4 PU MI-TR	10.07.09.00002

