

Plug union, elbow

STV-W G1/4-AG 8



Art.-Nr.: 10.08.02.00161




Technical data

Attribute	Value
Material	Nickel plated
Operating temperature	-20 ... 80 °C
Length L	24.00 mm
Thread G1	G1/4"-M
Outer hose diameter	8.00 mm

STV-W G1/4-AG 8

The push-in fittings are supplied in the desired design.



Design data

Attribute	Value
Length L1	33.20 mm
Length L	24.00 mm
Height H1	22.70 mm
Height H	14.80 mm
Outside diameter D1	14.6 mm
Nominal diameter dn	6.50 mm
Internal diameter d	8.00 mm
Thread G1	G1/4"-M
Thread length LG1	7.5 mm
Key width SW1	17.0 mm
Key width SW3	16.0 mm

Design data STV-W G1/4-AG 8



WWW.SCHMALZ.COM/10.08.02.00161

Art.-Nr.: 10.08.02.00161



Technical data

Attribute	Value
Weight	49.00 g
Material	Nickel plated
Design hose type	8-6
Pressure range (operating pressure) [bar]	-0.95 ... 15.00 bar
Operating temperature	-20 ... 80 °C
Product family	STV



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.08.02.00161



Ordering Data Accessories 10.08.02.00161

Typ		Item number
Compressed-air hose	VSL 8-6 PE BL	10.07.09.00015
Vacuum hose (meter)	VSL 8-6 PU MI-TR	10.07.09.00003