

Plug union, elbow

STV-W G3/8-AG 12



Art.-Nr.: 10.08.02.00163




Technical data

Attribute	Value
Material	Nickel plated
Operating temperature	-20 ... 80 °C
Length L	34.10 mm
Thread G1	G3/8"-M
Outer hose diameter	12.00 mm

STV-W G3/8-AG 12

The push-in fittings are supplied in the desired design.



Design data

Attribute	Value
Length L1	45.00 mm
Length L	34.10 mm
Height H1	27.90 mm
Height H	18.00 mm
Outside diameter D1	19.8 mm
Nominal diameter dn	9.00 mm
Internal diameter d	12.00 mm
Thread G1	G3/8"-M
Thread length LG1	7.5 mm
Key width SW1	20.0 mm
Key width SW3	20.0 mm

Design data STV-W G3/8-AG 12



WWW.SCHMALZ.COM/10.08.02.00163

Art.-Nr.: 10.08.02.00163



Technical data

Attribute	Value
Weight	98.00 g
Material	Nickel plated
Design hose type	12-9
Pressure range (operating pressure) [bar]	-0.95 ... 15.00 bar
Operating temperature	-20 ... 80 °C
Product family	STV



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.08.02.00163



Ordering Data Accessories 10.08.02.00163

Typ		Item number
Compressed-air hose	VSL 12-9 PE BL	10.07.09.00050
Vacuum hose (meter)	VSL 12-9 PU MI-TR	10.07.09.00037