




STV-WF M5-AG 4

The push-in fittings are supplied in the desired design.



Design data STV-WF M5-AG 4

Technical data

Attribute	Value
Material	Nickel plated
Operating temperature	-10 ... 70 °C
Length L	16.50 mm
Thread G1	M5-M
Outer hose diameter	4.00 mm

Design data

Attribute	Value
Length L1	20.10 mm
Length L	16.50 mm
Height H1	16.60 mm
Height H	8.40 mm
Outside diameter D1	8.6 mm
Nominal diameter dn	2.50 mm
Internal diameter d	4.00 mm
Thread G1	M5-M
Thread length LG1	3.5 mm
Key width SW1	8.0 mm
Key width SW3	8.5 mm

Art.-Nr.: 10.08.02.00165



Technical data

Attribute	Value
Weight	9.00 g
Material	Nickel plated
Design hose type	4-2
Pressure range (operating pressure) [bar]	-1.00 ... 15.00 bar
Operating temperature	-10 ... 70 °C
Product family	STV



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.08.02.00165



Ordering Data Accessories 10.08.02.00165

Typ		Item number
Compressed-air hose	VSL 4-2 PE BL	10.07.09.00013
Vacuum hose (meter)	VSL 4-2 PU MI-TR	10.07.09.00001
Vacuum hose (meter)	VSL 4-2.7 PA MI-TR	10.07.09.00063

