




STV-WF G1/4-AG 6

The push-in fittings are supplied in the desired design.



Design data STV-WF G1/4-AG 6

Technical data

Attribute	Value
Material	Nickel plated
Operating temperature	-10 ... 70 °C
Length L	22.90 mm
Thread G1	G1/4"-M
Outer hose diameter	6.00 mm

Design data

Attribute	Value
Length L1	32.90 mm
Length L	22.90 mm
Height H1	23.90 mm
Height H	9.80 mm
Outside diameter D1	11.8 mm
Nominal diameter dn	7.20 mm
Internal diameter d	6.00 mm
Thread G1	G1/4"-M
Thread length LG1	6.7 mm
Key width SW1	17.0 mm

Art.-Nr.: 10.08.02.00169



Technical data

Attribute	Value
Weight	57.00 g
Material	Nickel plated
Design hose type	6-4
Pressure range (operating pressure) [bar]	-0.95 ... 15.00 bar
Operating temperature	-10 ... 70 °C
Product family	STV



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.08.02.00169



Ordering Data Accessories 10.08.02.00169

Typ		Item number
Compressed-air hose	VSL 6-4 PE BL	10.07.09.00014
Vacuum hose (meter)	VSL 6-4 PTFE MI-TR	10.07.09.00157
Vacuum hose (meter)	VSL 6-4 PU MI-TR	10.07.09.00002