




STV-WF G1/8-AG 8

The push-in fittings are supplied in the desired design.



Design data STV-WF G1/8-AG 8

Technical data

Attribute	Value
Material	Nickel plated
Operating temperature	-10 ... 70 °C
Length L	23.40 mm
Thread G1	G1/8"-M
Outer hose diameter	8.00 mm

Design data

Attribute	Value
Length L1	31.30 mm
Length L	23.40 mm
Height H1	23.60 mm
Height H	9.80 mm
Outside diameter D1	14.3 mm
Nominal diameter dn	5.40 mm
Internal diameter d	8.00 mm
Thread G1	G1/8"-M
Thread length LG1	5.0 mm
Key width SW1	14.0 mm
Key width SW3	16.0 mm

Art.-Nr.: 10.08.02.00170



Technical data

Attribute	Value
Weight	43.00 g
Material	Nickel plated
Design hose type	8-6
Pressure range (operating pressure) [bar]	-0.95 ... 15.00 bar
Operating temperature	-10 ... 70 °C
Product family	STV



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.08.02.00170



Ordering Data Accessories 10.08.02.00170

Typ		Item number
Compressed-air hose	VSL 8-6 PE BL	10.07.09.00015
Vacuum hose (meter)	VSL 8-6 PU MI-TR	10.07.09.00003