

Plug union, straight

STV-GE G1/8-AG 6



Art.-Nr.: 10.08.02.00204




Technical data

Material	Brass
Operating temperature	-20 ... 80 °C
Length L	16.40 mm
Outside diameter D	11.40 mm
Thread G1	G1/8"-M
Outer hose diameter	6.00 mm

STV-GE G1/8-AG 6

The push-in fittings are supplied in the desired design.



Design data

Length L1	21.90 mm
Length L2	12.10 mm
Length L	16.40 mm
Outside diameter D	11.40 mm
Nominal diameter dn	4.00 mm
Internal diameter d	6.00 mm
Thread G1	G1/8"-M
Thread length LG1	5.5 mm
Key width SW1	13.0 mm

Design data STV-GE G1/8-AG 6



WWW.SCHMALZ.COM/10.08.02.00204

1

Plug union, straight

STV-GE G1/8-AG 6



Art.-Nr.: 10.08.02.00204



Technical data

Weight	11.00 g
Material	Brass
Design hose type	6-4
Pressure range (operating pressure) [bar]	-0.95 ... 15.00 bar
Operating temperature	-20 ... 80 °C
Product family	STV



Ordering Data Accessories 10.08.02.00204

Typ		Item number
Compressed-air hose	VSL 6-4 PE BL	10.07.09.00014
Vacuum hose (meter)	VSL 6-4 PTFE MI-TR	10.07.09.00157
Vacuum hose (meter)	VSL 6-4 PU MI-TR	10.07.09.00002



WWW.SCHMALZ.COM/10.08.02.00204