

Plug union, straight

STV-GE G1/8-AG 8



Art.-Nr.: 10.08.02.00206




Technical data

Attribute	Value
Material	Brass
Operating temperature	°C
Length L	20.70 mm
Outside diameter D	14.00 mm
Thread G1	G1/8"-M
Outer hose diameter	8.00 mm

STV-GE G1/8-AG 8

The push-in fittings are supplied in the desired design.



Design data

Attribute	Value
Length L1	26.20 mm
Length L2	16.40 mm
Length L	20.70 mm
Outside diameter D	14.00 mm
Nominal diameter dn	5.10 mm
Internal diameter d	8.00 mm
Thread G1	G1/8"-M
Thread length LG1	5.5 mm
Key width SW1	14.0 mm

Design data STV-GE G1/8-AG 8



WWW.SCHMALZ.COM/10.08.02.00206

Plug union, straight

STV-GE G1/8-AG 8



Art.-Nr.: 10.08.02.00206



Technical data

Attribute	Value
Weight	16.30 g
Material	Brass
Design hose type	8-6
Pressure range (operating pressure) [bar]	bar
Operating temperature	°C
Product family	STV



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.08.02.00206



Ordering Data Accessories 10.08.02.00206

Typ		Item number
Compressed-air hose	VSL 8-6 PE BL	10.07.09.00015
Vacuum hose (meter)	VSL 8-6 PU MI-TR	10.07.09.00003



WWW.SCHMALZ.COM/10.08.02.00206