

Plug union, straight

STV-GE G1/4-AG 8



Art.-Nr.: 10.08.02.00207




Technical data

Attribute	Value
Material	Brass
Operating temperature	-20 ... 80 °C
Length L	17.80 mm
Outside diameter D	13.90 mm
Thread G1	G1/4"-M
Outer hose diameter	8.00 mm

STV-GE G1/4-AG 8

The push-in fittings are supplied in the desired design.



Design data

Attribute	Value
Length L1	25.20 mm
Length L2	12.80 mm
Length L	17.80 mm
Outside diameter D	13.90 mm
Nominal diameter dn	6.00 mm
Internal diameter d	8.00 mm
Thread G1	G1/4"-M
Thread length LG1	7.4 mm
Key width SW1	17.0 mm

Design data STV-GE G1/4-AG 8



WWW.SCHMALZ.COM/10.08.02.00207

Plug union, straight

STV-GE G1/4-AG 8



Art.-Nr.: 10.08.02.00207



Technical data

Attribute	Value
Weight	19.00 g
Material	Brass
Design hose type	8-6
Pressure range (operating pressure) [bar]	-0.95 ... 15.00 bar
Operating temperature	-20 ... 80 °C
Product family	STV



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.08.02.00207



Ordering Data Accessories 10.08.02.00207

Typ		Item number
Compressed-air hose	VSL 8-6 PE BL	10.07.09.00015
Vacuum hose (meter)	VSL 8-6 PU MI-TR	10.07.09.00003



WWW.SCHMALZ.COM/10.08.02.00207