

Plug union, straight

STV-GE G3/8-AG 12



Art.-Nr.: 10.08.02.00209




Technical data

Attribute	Value
Material	Brass
Operating temperature	-20 ... 80 °C
Length L	23.60 mm
Outside diameter D	19.50 mm
Thread G1	G3/8"-M
Outer hose diameter	12.00 mm

STV-GE G3/8-AG 12

The push-in fittings are supplied in the desired design.



Design data

Attribute	Value
Length L1	31.00 mm
Length L2	17.60 mm
Length L	23.60 mm
Outside diameter D	19.50 mm
Nominal diameter dn	9.00 mm
Internal diameter d	12.00 mm
Thread G1	G3/8"-M
Thread length LG1	7.4 mm
Key width SW1	20.0 mm

Design data STV-GE G3/8-AG 12



WWW.SCHMALZ.COM/10.08.02.00209

Plug union, straight

STV-GE G3/8-AG 12



Art.-Nr.: 10.08.02.00209



Technical data

Attribute	Value
Weight	35.00 g
Material	Brass
Design hose type	12-9
Pressure range (operating pressure) [bar]	-0.95 ... 15.00 bar
Operating temperature	-20 ... 80 °C
Product family	STV



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.08.02.00209



Ordering Data Accessories 10.08.02.00209

Typ		Item number
Compressed-air hose	VSL 12-9 PE BL	10.07.09.00050
Vacuum hose (meter)	VSL 12-9 PU MI-TR	10.07.09.00037



WWW.SCHMALZ.COM/10.08.02.00209