

Plug union, straight

STV-GE G3/8-AG 14



Art.-Nr.: 10.08.02.00211




Technical data

Attribute	Value
Material	Brass
Operating temperature	-20 ... 80 °C
Length L	30.50 mm
Outside diameter D	21.50 mm
Thread G1	G3/8"-M
Outer hose diameter	14.00 mm

STV-GE G3/8-AG 14

The push-in fittings are supplied in the desired design.



Design data

Attribute	Value
Length L1	37.80 mm
Length L2	22.10 mm
Length L	30.50 mm
Outside diameter D	21.50 mm
Nominal diameter dn	10.30 mm
Internal diameter d	14.00 mm
Thread G1	G3/8"-M
Thread length LG1	7.3 mm
Key width SW1	22.0 mm

Design data STV-GE G3/8-AG 14



WWW.SCHMALZ.COM/10.08.02.00211

Plug union, straight

STV-GE G3/8-AG 14



Art.-Nr.: 10.08.02.00211



Technical data

Attribute	Value
Weight	50.00 g
Material	Brass
Design hose type	14-11
Pressure range (operating pressure) [bar]	-0.95 ... 15.00 bar
Operating temperature	-20 ... 80 °C
Product family	STV



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.08.02.00211



Ordering Data Accessories 10.08.02.00211

Typ	Item number
Vacuum hose (meter)	VSL 14-11 PU MI-TR 10.07.09.00038



WWW.SCHMALZ.COM/10.08.02.00211