

Plug union, elbow


STV-W M5-AG 6

Art.-Nr.: 10.08.02.00235



STV-W M5-AG 6

The push-in fittings are supplied in the desired design.



Design data STV-W M5-AG 6

Technical data

Attribute	Value
Material	Nickel plated
Operating temperature	-20 ... 80 °C
Length L	19.70 mm
Thread G1	M5-M
Outer hose diameter	6.00 mm

Design data

Attribute	Value
Length L1	24.70 mm
Length L	19.70 mm
Height H1	13.60 mm
Height H	8.70 mm
Outside diameter D1	9.9 mm
Nominal diameter dn	2.50 mm
Internal diameter d	6.00 mm
Thread G1	M5-M
Thread length LG1	4.7 mm
Key width SW1	8.0 mm
Key width SW3	10.0 mm



WWW.SCHMALZ.COM/10.08.02.00235

Art.-Nr.: 10.08.02.00235



Technical data

Attribute	Value
Weight	16.00 g
Material	Nickel plated
Design hose type	6-4
Pressure range (operating pressure) [bar]	-0.95 ... 15.00 bar
Operating temperature	-20 ... 80 °C
Product family	STV



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.08.02.00235



Ordering Data Accessories 10.08.02.00235

Typ		Item number
Compressed-air hose	VSL 6-4 PE BL	10.07.09.00014
Vacuum hose (meter)	VSL 6-4 PTFE MI-TR	10.07.09.00157
Vacuum hose (meter)	VSL 6-4 PU MI-TR	10.07.09.00002