

Plug union, straight

STV-GE G1/2-AG 10



Art.-Nr.: 10.08.02.00253




Technical data

Attribute	Value
Material	Brass
Operating temperature	-20 ... 80 °C
Length L	18.50 mm
Outside diameter D	16.50 mm
Thread G1	G1/2"-M
Outer hose diameter	10.00 mm

STV-GE G1/2-AG 10

The push-in fittings are supplied in the desired design.



Design data

Attribute	Value
Length L1	28.00 mm
Length L2	12.50 mm
Length L	18.50 mm
Outside diameter D	16.50 mm
Nominal diameter dn	8.00 mm
Internal diameter d	10.00 mm
Thread G1	G1/2"-M
Thread length LG1	9.5 mm
Key width SW1	24.0 mm

Design data STV-GE G1/2-AG 10



WWW.SCHMALZ.COM/10.08.02.00253

Plug union, straight

STV-GE G1/2-AG 10



Art.-Nr.: 10.08.02.00253



Technical data

Attribute	Value
Weight	43.00 g
Material	Brass
Design hose type	10-7
Pressure range (operating pressure) [bar]	-0.95 ... 15.00 bar
Operating temperature	-20 ... 80 °C
Product family	STV



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.08.02.00253



Ordering Data Accessories 10.08.02.00253

Typ		Item number
Vacuum hose (meter)	VSL 10-7 PE MI-TR	10.07.09.00083
Vacuum hose (meter)	VSL 10-7 PU MI-TR	10.07.09.00084



WWW.SCHMALZ.COM/10.08.02.00253