




STV-WF G1/8-AG 10

The push-in fittings are supplied in the desired design.



Design data STV-WF G1/8-AG 10

Technical data

Attribute	Value
Material	Nickel plated
Operating temperature	-10 ... 70 °C
Length L	25.20 mm
Thread G1	G1/8"-M
Outer hose diameter	10.00 mm

Design data

Attribute	Value
Length L1	33.60 mm
Length L	25.20 mm
Height H1	23.60 mm
Height H	9.80 mm
Outside diameter D1	16.7 mm
Nominal diameter dn	10.00 mm
Internal diameter d	10.00 mm
Thread G1	G1/8"-M
Thread length LG1	5.0 mm
Key width SW1	14.0 mm
Key width SW3	17.0 mm

Plug union, elbow

STV-WF G1/8-AG 10



Art.-Nr.: 10.08.02.00257



Technical data

Attribute	Value
Weight	49.00 g
Material	Nickel plated
Design hose type	10-7
Pressure range (operating pressure) [bar]	-0.95 ... 15.00 bar
Operating temperature	-10 ... 70 °C
Product family	STV



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.08.02.00257



Ordering Data Accessories 10.08.02.00257

Typ		Item number
Vacuum hose (meter)	VSL 10-7 PE MI-TR	10.07.09.00083
Vacuum hose (meter)	VSL 10-7 PU MI-TR	10.07.09.00084



WWW.SCHMALZ.COM/10.08.02.00257