

Plug union, straight

STV-GE G1/2-AG 14



Art.-Nr.: 10.08.02.00300




Technical data

Attribute	Value
Material	Brass
Operating temperature	°C
Length L	25.00 mm
Outside diameter D	21.50 mm
Thread G1	G1/2"-M
Outer hose diameter	14.00 mm

STV-GE G1/2-AG 14

The push-in fittings are supplied in the desired design.



Design data

Attribute	Value
Length L1	34.50 mm
Length L2	19.00 mm
Length L	25.00 mm
Outside diameter D	21.50 mm
Nominal diameter dn	10.30 mm
Internal diameter d	14.00 mm
Thread G1	G1/2"-M
Thread length LG1	9.6 mm
Key width SW1	24.0 mm

Design data STV-GE G1/2-AG 14



WWW.SCHMALZ.COM/10.08.02.00300

Plug union, straight

STV-GE G1/2-AG 14



Art.-Nr.: 10.08.02.00300



Technical data

Attribute	Value
Weight	52.70 g
Material	Brass
Design hose type	14-11
Pressure range (operating pressure) [bar]	bar
Operating temperature	°C
Product family	STV



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.08.02.00300



Ordering Data Accessories 10.08.02.00300

Typ	Item number
Vacuum hose (meter)	VSL 14-11 PU MI-TR 10.07.09.00038



WWW.SCHMALZ.COM/10.08.02.00300