

Plug union, elbow

STV-W G1/8-AG 10



Art.-Nr.: 10.08.02.00306




Technical data

Attribute	Value
Material	Plastics
Operating temperature	0 ... 60 °C
Length L	26.50 mm
Thread G1	G1/8"-M
Outer hose diameter	10.00 mm

STV-W G1/8-AG 10

The push-in fittings are supplied in the desired design.



Design data

Attribute	Value
Length L1	34.50 mm
Length L	26.50 mm
Height H1	26.00 mm
Height H	16.50 mm
Outside diameter D1	19.0 mm
Nominal diameter dn	6.00 mm
Internal diameter d	10.00 mm
Thread G1	G1/8"-M
Thread length LG1	5.0 mm
Key width SW1	16.0 mm

Design data STV-W G1/8-AG 10



WWW.SCHMALZ.COM/10.08.02.00306

Plug union, elbow

STV-W G1/8-AG 10



Art.-Nr.: 10.08.02.00306



Technical data

Attribute	Value
Weight	28.00 g
Material	Plastics
Design hose type	10-7
Pressure range (operating pressure) [bar]	1.00 ... 10.00 bar
Operating temperature	0 ... 60 °C
Product family	STV



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.08.02.00306



WWW.SCHMALZ.COM/10.08.02.00306