

Plug union, straight

STV-GE G1/8-AG 6 HT



Art.-Nr.: 10.08.02.00389




Technical data

Attribute	Value
Material	Brass
Operating temperature	-20 ... 120 °C
Length L	19.00 mm
Outside diameter D	11.60 mm
Thread G1	G1/8"-M
Outer hose diameter	6.00 mm

STV-GE G1/8-AG 6 HT

The push-in fittings are supplied in the desired design.



Design data

Attribute	Value
Length L1	24.50 mm
Length L2	15.00 mm
Length L	19.00 mm
Outside diameter D	11.60 mm
Nominal diameter dn	6.00 mm
Internal diameter d	6.00 mm
Thread G1	G1/8"-M
Thread length LG1	5.5 mm
Key width SW1	13.0 mm

Design data STV-GE G1/8-AG 6 HT



WWW.SCHMALZ.COM/10.08.02.00389

Plug union, straight

STV-GE G1/8-AG 6 HT



Art.-Nr.: 10.08.02.00389



Technical data

Attribute	Value
Weight	12.00 g
Material	Brass
Design hose type	6-4
Pressure range (operating pressure) [bar]	-0.95 ... 24.00 bar
Operating temperature	-20 ... 120 °C
Product family	STV



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.08.02.00389



Ordering Data Accessories 10.08.02.00389

Typ		Item number
Compressed-air hose	VSL 6-4 PE BL	10.07.09.00014
Vacuum hose (meter)	VSL 6-4 PTFE MI-TR	10.07.09.00157
Vacuum hose (meter)	VSL 6-4 PU MI-TR	10.07.09.00002



WWW.SCHMALZ.COM/10.08.02.00389