

Plug union, elbow

STV-W G1/8-AG 8



Art.-Nr.: 10.08.02.00409




Technical data

Attribute	Value
Material	Plastics
Operating temperature	0 ... 80 °C
Length L	22.70 mm
Thread G1	G1/8"-M
Outer hose diameter	8.00 mm

STV-W G1/8-AG 8

The push-in fittings are supplied in the desired design.



Design data

Attribute	Value
Length L1	30.00 mm
Length L	22.70 mm
Height H1	23.30 mm
Height H	16.00 mm
Outside diameter D1	13.8 mm
Nominal diameter dn	6.00 mm
Internal diameter d	8.00 mm
Thread G1	G1/8"-M
Thread length LG1	8.0 mm
Key width SW1	12.0 mm

Design data STV-W G1/8-AG 8



WWW.SCHMALZ.COM/10.08.02.00409

Plug union, elbow

STV-W G1/8-AG 8



Art.-Nr.: 10.08.02.00409



Technical data

Attribute	Value
Weight	14.00 g
Material	Plastics
Design hose type	8-6
Pressure range (operating pressure) [bar]	-1.00 ... 14.00 bar
Operating temperature	0 ... 80 °C
Product family	STV



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.08.02.00409



WWW.SCHMALZ.COM/10.08.02.00409