

Plug union, elbow

## STV-W G1/4-AG 6



Art.-Nr.: 10.08.02.00462




### Technical data

Material	Plastics
Operating temperature	0 ... 60 °C
Length L	19.50 mm
Thread G1	G 1/4"-M
Outer hose diameter	6.00 mm

STV-W G1/4-AG 6

The push-in fittings are supplied in the desired design.



### Design data

Length L1	27.50 mm
Length L	19.50 mm
Height H1	17.10 mm
Height H	10.70 mm
Outside diameter D1	14.0 mm
Nominal diameter dn	6.00 mm
Internal diameter d	6.00 mm
Thread G1	G 1/4"-M
Thread length LG1	6.0 mm
Key width SW1	16.0 mm

Design data STV-W G1/4-AG 6



[WWW.SCHMALZ.COM/10.08.02.00462](http://WWW.SCHMALZ.COM/10.08.02.00462)

1

Plug union, elbow

## STV-W G1/4-AG 6



Art.-Nr.: 10.08.02.00462



### Technical data

Weight	19.30 g
Material	Plastics
Design hose type	6-4
Pressure range (operating pressure) [bar]	-0.95 ... 10.00 bar
Operating temperature	0 ... 60 °C
Product family	STV



[WWW.SCHMALZ.COM/10.08.02.00462](http://WWW.SCHMALZ.COM/10.08.02.00462)