

Plug union, straight

STV-GE M5-AG 4



Art.-Nr.: 10.08.02.00468




Technical data

Attribute	Value
Material	Brass
Operating temperature	°C
Length L	15.00 mm
Outside diameter D	7.90 mm
Thread G1	M5-M
Outer hose diameter	4.00 mm

STV-GE M5-AG 4

The push-in fittings are supplied in the desired design.



Design data

Attribute	Value
Length L1	19.50 mm
Length L	15.00 mm
Outside diameter D	7.90 mm
Nominal diameter dn	2.00 mm
Internal diameter d	4.00 mm
Thread G1	M5-M
Thread length LG1	4.5 mm

Design data STV-GE M5-AG 4



WWW.SCHMALZ.COM/10.08.02.00468

Plug union, straight

STV-GE M5-AG 4



Art.-Nr.: 10.08.02.00468



Technical data

Attribute	Value
Material	Brass
Design hose type	4-2
Pressure range (operating pressure) [bar]	bar
Operating temperature	°C
Product family	STV



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.08.02.00468



WWW.SCHMALZ.COM/10.08.02.00468