

Plug union, straight

## STV-GE M7-AG 6



Art.-Nr.: 10.08.02.00469




### Technical data

| Attribute             | Value    |
|-----------------------|----------|
| Material              | Brass    |
| Operating temperature | °C       |
| Length L              | 18.50 mm |
| Outside diameter D    | 9.90 mm  |
| Thread G1             | M7-M     |
| Outer hose diameter   | 6.00 mm  |

STV-GE M7-AG 6

The push-in fittings are supplied in the desired design.



### Design data

| Attribute           | Value    |
|---------------------|----------|
| Length L1           | 23.50 mm |
| Length L            | 18.50 mm |
| Outside diameter D  | 9.90 mm  |
| Nominal diameter dn | 4.00 mm  |
| Internal diameter d | 6.00 mm  |
| Thread G1           | M7-M     |
| Thread length LG1   | 5.0 mm   |

Design data STV-GE M7-AG 6



[WWW.SCHMALZ.COM/10.08.02.00469](http://WWW.SCHMALZ.COM/10.08.02.00469)

Plug union, straight

## STV-GE M7-AG 6



Art.-Nr.: 10.08.02.00469



### Technical data

| Attribute                                 | Value |
|-------------------------------------------|-------|
| Material                                  | Brass |
| Design hose type                          | 6-4   |
| Pressure range (operating pressure) [bar] | bar   |
| Operating temperature                     | °C    |
| Product family                            | STV   |



### Further documentation

CAD data and other documents relating to the article can be found at: [www.schmalz.com/10.08.02.00469](http://www.schmalz.com/10.08.02.00469)



[WWW.SCHMALZ.COM/10.08.02.00469](http://WWW.SCHMALZ.COM/10.08.02.00469)