

Plug union, elbow

STV-W G1/8-AG 8 HT



Art.-Nr.: 10.08.02.00650




Technical data

Attribute	Value
Material	Brass
Operating temperature	-20 ... 120 °C
Length L	27.00 mm
Thread G1	G1/8"-M
Outer hose diameter	8.00 mm

STV-W G1/8-AG 8 HT

The push-in fittings are supplied in the desired design.



Design data

Attribute	Value
Length L1	35.00 mm
Length L	27.00 mm
Height H1	20.70 mm
Height H	13.40 mm
Outside diameter D1	14.8 mm
Internal diameter d	8.00 mm
Thread G1	G1/8"-M
Thread length LG1	5.5 mm
Key width SW1	14.0 mm
Key width SW3	16.0 mm

Design data STV-W G1/8-AG 8 HT



WWW.SCHMALZ.COM/10.08.02.00650

Plug union, elbow

STV-W G1/8-AG 8 HT



Art.-Nr.: 10.08.02.00650



Technical data

Attribute	Value
Weight	41.00 g
Material	Brass
Pressure range (operating pressure) [bar]	-0.95 ... 24.00 bar
Operating temperature	-20 ... 120 °C
Product family	STV
Design hose type	8/6



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.08.02.00650



Ordering Data Accessories 10.08.02.00650

Typ		Item number
Compressed-air hose	VSL 6-4 PE BL	10.07.09.00014
Vacuum hose (meter)	VSL 6-4 PU MI-TR	10.07.09.00002
Vacuum hose (meter)	VSL 6-4 PTFE MI-TR	10.07.09.00157



WWW.SCHMALZ.COM/10.08.02.00650