

Plug union, elbow

## STV-W G1/8-AG 4



Art.-Nr.: 10.08.03.00231




### Technical data

Material	Plastics
Operating temperature	0 ... 60 °C
Length L	18.50 mm
Thread G1	G 1/8"-M
Outer hose diameter	4.00 mm

STV-W G1/8-AG 4

The push-in fittings are supplied in the desired design.



### Design data

Length L1	24.80 mm
Length L	18.50 mm
Height H1	15.50 mm
Height H	9.50 mm
Outside diameter D1	12.0 mm
Nominal diameter dn	2.00 mm
Internal diameter d	4.00 mm
Thread G1	G 1/8"-M
Thread length LG1	5.0 mm
Key width SW1	13.0 mm

Design data STV-W G1/8-AG 4



[WWW.SCHMALZ.COM/10.08.03.00231](http://WWW.SCHMALZ.COM/10.08.03.00231)

Plug union, elbow

## STV-W G1/8-AG 4



Art.-Nr.: 10.08.03.00231



### Technical data

Weight	12.30 g
Material	Plastics
Design hose type	4-2
Pressure range (operating pressure) [bar]	0.95 ... 10.00 bar
Operating temperature	0 ... 60 °C
Product family	STV



[WWW.SCHMALZ.COM/10.08.03.00231](http://WWW.SCHMALZ.COM/10.08.03.00231)