

Plug union, elbow

STV-W G1/4-AG 4



Art.-Nr.: 10.08.03.00232




Technical data

Material	Plastics
Operating temperature	0 ... 60 °C
Length L	18.50 mm
Thread G1	G 1/4"-M
Outer hose diameter	4.00 mm

STV-W G1/4-AG 4

The push-in fittings are supplied in the desired design.



Design data

Length L1	26.30 mm
Length L	18.50 mm
Height H1	15.50 mm
Height H	9.50 mm
Outside diameter D1	12.0 mm
Nominal diameter dn	2.00 mm
Internal diameter d	4.00 mm
Thread G1	G 1/4"-M
Thread length LG1	6.0 mm
Key width SW1	16.0 mm

Design data STV-W G1/4-AG 4



WWW.SCHMALZ.COM/10.08.03.00232

1

Plug union, elbow

STV-W G1/4-AG 4



Art.-Nr.: 10.08.03.00232



Technical data

Weight	17.10 g
Material	Plastics
Design hose type	4-2
Pressure range (operating pressure) [bar]	0.95 ... 10.00 bar
Operating temperature	0 ... 60 °C
Product family	STV



WWW.SCHMALZ.COM/10.08.03.00232