

Plug union, elbow

STV-W G1/4-AG 8



Art.-Nr.: 10.08.03.00233




Technical data

| | |
|-----------------------|-------------|
| Material | Plastics |
| Operating temperature | 0 ... 60 °C |
| Length L | 22.60 mm |
| Thread G1 | G 1/4"-M |
| Outer hose diameter | 8.00 mm |

STV-W G1/4-AG 8

The push-in fittings are supplied in the desired design.



Design data

| | |
|---------------------|----------|
| Length L1 | 30.70 mm |
| Length L | 22.60 mm |
| Height H1 | 19.50 mm |
| Height H | 11.50 mm |
| Outside diameter D1 | 16.0 mm |
| Nominal diameter dn | 6.00 mm |
| Internal diameter d | 8.00 mm |
| Thread G1 | G 1/4"-M |
| Thread length LG1 | 6.0 mm |
| Key width SW1 | 16.0 mm |

Design data STV-W G1/4-AG 8



WWW.SCHMALZ.COM/10.08.03.00233

Plug union, elbow

STV-W G1/4-AG 8



Art.-Nr.: 10.08.03.00233



Technical data

| | |
|---|--------------------|
| Weight | 23.10 g |
| Material | Plastics |
| Design hose type | 8-6 |
| Pressure range (operating pressure) [bar] | 0.95 ... 10.00 bar |
| Operating temperature | 0 ... 60 °C |
| Product family | STV |



WWW.SCHMALZ.COM/10.08.03.00233