

Plug union, elbow

## STV-W G1/4-AG 10



Art.-Nr.: 10.08.03.00235




### Technical data

Material	Plastics
Operating temperature	0 ... 60 °C
Length L	27.00 mm
Thread G1	G 1/4"-M
Outer hose diameter	10.00 mm

STV-W G1/4-AG 10

The push-in fittings are supplied in the desired design.



### Design data

Length L1	34.50 mm
Length L	27.00 mm
Height H1	26.10 mm
Height H	16.50 mm
Outside diameter D1	19.0 mm
Nominal diameter dn	7.00 mm
Internal diameter d	10.00 mm
Thread G1	G 1/4"-M
Thread length LG1	6.0 mm
Key width SW1	16.0 mm

Design data STV-W G1/4-AG 10



[WWW.SCHMALZ.COM/10.08.03.00235](http://WWW.SCHMALZ.COM/10.08.03.00235)

Plug union, elbow

## STV-W G1/4-AG 10



Art.-Nr.: 10.08.03.00235



### Technical data

Weight	28.70 g
Material	Plastics
Design hose type	10-7
Pressure range (operating pressure) [bar]	0.95 ... 10.00 bar
Operating temperature	0 ... 60 °C
Product family	STV



[WWW.SCHMALZ.COM/10.08.03.00235](http://WWW.SCHMALZ.COM/10.08.03.00235)