

RMQC 50 URe DIO WB-M8-8 NPN MATCH

Art.-Nr.: 10.08.09.00001




Technical data

Attribute	Value
Construction vacuum switch	NPN switching
Inputs / outputs	digital input / output
Electrical connection	Elb fem conn M8, 8 pol
Version	Quick-change system MATCH
Dmk	50.0 mm
Type	UR3e-16e
for	Universal Robots e
Additional function Plant equipment	Freedrive

RMQC 50 URe DIO WB-M8-8 NPN MATCH

The RMQC quick-change module is supplied ready for connection.
Suitable vacuum generator must be ordered separately.

Design data



Attribute	Value
Height H1	24.00 mm
Height H	21.00 mm
Outside diameter D2	31.5 mm
Outside diameter D	75.00 mm
Internal diameter d	6.40 mm
Thread G1	M8-F
Thread G2	M7-F
Dmk	50.0 mm
Cable length	200.00 mm
Thread G4	M4-F

Design data RMQC 50 URe DIO WB-M8-8 NPN MATCH



Art.-Nr.: 10.08.09.00001

**Technical data**

Attribute	Value
Shape mounting elements	Fluid channel closed
Construction vacuum switch	NPN switching
Inputs / outputs	digital input / output
Weight	260.0 g
Operating temperature	5 ... 60 °C
Version	Quick-change system MATCH
Electrical connection	WB-M8-8
Type	UR3e-16e
with	E-transfer electrical / pneumatic
for	Universal Robots e
Force axial (max)	500.0 N
Moment (Y)	40.0 Nm
Axle offset max	1.0 mm
Number of load cycles	100,000.00
Tightening force	50.0 N
Dissolving power	0.0 N

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.08.09.00001**Ordering Data Accessories 10.08.09.00001**

Typ	Artikelnummer
Building group Solenoid valve	VENT-BGR EMVP-5 3/2 NC 24V-DC
	10.08.09.00032

