




Technical data

Material	Brass
Operating temperature	-20 ... 80 °C
Length L	34.00 mm
Outer hose diameter	4.00 mm

SVB-T 4

The push-in fittings are supplied in the desired design.



Design data

Length L	34.00 mm
Height H1	20.60 mm
Height H	16.30 mm
Outside diameter D1	8.6 mm
Internal diameter d	4.00 mm

Design data SVB-T 4

Art.-Nr.: 10.09.02.00020



Technical data

Weight	13.00 g
Material	Brass
Design hose type	4-2
Pressure range (operating pressure) [bar]	-1.00 ... 15.00 bar
Operating temperature	-20 ... 80 °C
Product family	STV



Ordering Data Accessories 10.09.02.00020

Typ		Item number
Compressed-air hose	VSL 4-2 PE BL	10.07.09.00013
Vacuum hose (meter)	VSL 4-2 PU MI-TR	10.07.09.00001
Vacuum hose (meter)	VSL 4-2.7 PA MI-TR	10.07.09.00063

