




SVB-T 8

The push-in fittings are supplied in the desired design.



Design data SVB-T 8

Technical data

Attribute	Value
Material	Brass
Operating temperature	-20 ... 80 °C
Length L	49.00 mm
Outer hose diameter	8.00 mm

Design data

Attribute	Value
Length L	49.00 mm
Height H1	31.90 mm
Height H	24.70 mm
Outside diameter D1	14.4 mm
Internal diameter d	8.00 mm

Art.-Nr.: 10.09.02.00022



Technical data

Attribute	Value
Weight	43.00 g
Material	Brass
Design hose type	8-6
Pressure range (operating pressure) [bar]	-0.95 ... 15.00 bar
Operating temperature	-20 ... 80 °C
Product family	STV



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.09.02.00022



Ordering Data Accessories 10.09.02.00022

Typ		Item number
Compressed-air hose	VSL 8-6 PE BL	10.07.09.00015
Vacuum hose (meter)	VSL 8-6 PU MI-TR	10.07.09.00003