




Technical data

Attribute	Value
Material	Brass
Operating temperature	-20 ... 80 °C
Length L	69.00 mm
Outer hose diameter	12.00 mm

SVB-T 12

The push-in fittings are supplied in the desired design.



Design data

Attribute	Value
Length L	69.00 mm
Height H1	44.00 mm
Height H	34.00 mm
Outside diameter D1	19.9 mm
Internal diameter d	12.00 mm

Design data SVB-T 12

Art.-Nr.: 10.09.02.00023



Technical data

Attribute	Value
Weight	115.00 g
Material	Brass
Design hose type	12-9
Pressure range (operating pressure) [bar]	-0.95 ... 15.00 bar
Operating temperature	-20 ... 80 °C
Product family	STV



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.09.02.00023



Ordering Data Accessories 10.09.02.00023

Typ		Item number
Compressed-air hose	VSL 12-9 PE BL	10.07.09.00050
Vacuum hose (meter)	VSL 12-9 PU MI-TR	10.07.09.00037