




Technical data

Attribute	Value
Material	Brass
Operating temperature	-20 ... 80 °C
Length L	55.50 mm
Outer hose diameter	10.00 mm

SVB-T 10

The push-in fittings are supplied in the desired design.



Design data

Attribute	Value
Length L	55.50 mm
Height H1	36.00 mm
Height H	27.70 mm
Outside diameter D1	16.7 mm
Internal diameter d	10.00 mm

Design data SVB-T 10

Art.-Nr.: 10.09.02.00025



Technical data

Attribute	Value
Weight	59.00 g
Material	Brass
Design hose type	10-7
Pressure range (operating pressure) [bar]	-0.95 ... 15.00 bar
Operating temperature	-20 ... 80 °C
Product family	STV



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.09.02.00025



Ordering Data Accessories 10.09.02.00025

Typ		Item number
Vacuum hose (meter)	VSL 10-7 PE MI-TR	10.07.09.00083
Vacuum hose (meter)	VSL 10-7 PU MI-TR	10.07.09.00084