




Technical data

Attribute	Value
Material	Brass
Operating temperature	°C
Length L	32.50 mm
Thread G1	G1/8"-M
Outer hose diameter	4.00 mm

STV-T G1/8-AG 4

The push-in fittings are supplied in the desired design.



Design data

Attribute	Value
Length L	32.50 mm
Height H1	16.00 mm
Height H	11.70 mm
Outside diameter D1	8.7 mm
Nominal diameter dn	3.00 mm
Internal diameter d	4.00 mm
Thread G1	G1/8"-M
Thread length LG1	5.5 mm
Key width SW1	13.0 mm

Design data STV-T G1/8-AG 4

Plug union, T

STV-T G1/8-AG 4



Art.-Nr.: 10.09.02.00039



Technical data

Attribute	Value
Weight	19.30 g
Material	Brass
Design hose type	4-2
Pressure range (operating pressure) [bar]	bar
Operating temperature	°C
Product family	STV



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.09.02.00039



Ordering Data Accessories 10.09.02.00039

Typ		Item number
Compressed-air hose	VSL 4-2 PE BL	10.07.09.00013
Vacuum hose (meter)	VSL 4-2 PU MI-TR	10.07.09.00001
Vacuum hose (meter)	VSL 4-2.7 PA MI-TR	10.07.09.00063



WWW.SCHMALZ.COM/10.09.02.00039