




Technical data

Attribute	Value
Material	Brass
Operating temperature	°C
Length L	41.50 mm
Thread G1	G1/8"-M
Outer hose diameter	6.00 mm

STV-T G1/8-AG 6

The push-in fittings are supplied in the desired design.



Design data

Attribute	Value
Length L	41.50 mm
Height H1	20.00 mm
Height H	14.00 mm
Outside diameter D1	12.0 mm
Nominal diameter dn	4.00 mm
Internal diameter d	6.00 mm
Thread G1	G1/8"-M
Thread length LG1	5.5 mm
Key width SW1	13.0 mm

Design data STV-T G1/8-AG 6

Plug union, T

STV-T G1/8-AG 6



Art.-Nr.: 10.09.02.00040



Technical data

Attribute	Value
Weight	35.40 g
Material	Brass
Design hose type	6-4
Pressure range (operating pressure) [bar]	bar
Operating temperature	°C
Product family	STV



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.09.02.00040



Ordering Data Accessories 10.09.02.00040

Typ		Item number
Compressed-air hose	VSL 6-4 PE BL	10.07.09.00014
Vacuum hose (meter)	VSL 6-4 PTFE MI-TR	10.07.09.00157
Vacuum hose (meter)	VSL 6-4 PU MI-TR	10.07.09.00002



WWW.SCHMALZ.COM/10.09.02.00040