

Plug union, T

STV-T G1/8-AG 8

Art.-Nr.: 10.09.02.00041




Technical data

Attribute	Value
Material	Brass
Operating temperature	°C
Length L	48.70 mm
Thread G1	G1/8"-M
Outer hose diameter	8.00 mm

STV-T G1/8-AG 8

The push-in fittings are supplied in the desired design.



Design data STV-T G1/8-AG 8

Design data

Attribute	Value
Length L	48.70 mm
Height H1	22.00 mm
Height H	15.00 mm
Outside diameter D1	14.1 mm
Nominal diameter dn	5.50 mm
Internal diameter d	8.00 mm
Thread G1	G1/8"-M
Thread length LG1	5.5 mm
Key width SW1	13.0 mm



WWW.SCHMALZ.COM/10.09.02.00041

Plug union, T

STV-T G1/8-AG 8



Art.-Nr.: 10.09.02.00041



Technical data

Attribute	Value
Weight	51.60 g
Material	Brass
Design hose type	8-6
Pressure range (operating pressure) [bar]	bar
Operating temperature	°C
Product family	STV



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.09.02.00041



Ordering Data Accessories 10.09.02.00041

Typ		Item number
Compressed-air hose	VSL 8-6 PE BL	10.07.09.00015
Vacuum hose (meter)	VSL 8-6 PU MI-TR	10.07.09.00003



WWW.SCHMALZ.COM/10.09.02.00041