




Technical data

Attribute	Value
Material	Brass
Operating temperature	°C
Length L	54.90 mm
Thread G1	G1/4"-M
Outer hose diameter	10.00 mm

STV-T G1/4-AG 10

The push-in fittings are supplied in the desired design.



Design data

Attribute	Value
Length L	54.90 mm
Height H1	23.20 mm
Height H	15.00 mm
Outside diameter D1	16.5 mm
Nominal diameter dn	8.00 mm
Internal diameter d	10.00 mm
Thread G1	G1/4"-M
Thread length LG1	7.6 mm
Key width SW1	17.0 mm

Design data STV-T G1/4-AG 10

Plug union, T

STV-T G1/4-AG 10



Art.-Nr.: 10.09.02.00044



Technical data

Attribute	Value
Weight	70.30 g
Material	Brass
Design hose type	10-7
Pressure range (operating pressure) [bar]	bar
Operating temperature	°C
Product family	STV



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.09.02.00044



Ordering Data Accessories 10.09.02.00044

Typ		Item number
Vacuum hose (meter)	VSL 10-7 PE MI-TR	10.07.09.00083
Vacuum hose (meter)	VSL 10-7 PU MI-TR	10.07.09.00084



WWW.SCHMALZ.COM/10.09.02.00044