




Technical data

Attribute	Value
Material	Brass
Operating temperature	°C
Length L	69.00 mm
Thread G1	G1/4"-M
Outer hose diameter	12.00 mm

STV-T G1/4-AG 12

The push-in fittings are supplied in the desired design.



Design data

Attribute	Value
Length L	69.00 mm
Height H1	26.60 mm
Height H	16.80 mm
Outside diameter D1	19.6 mm
Nominal diameter dn	8.40 mm
Internal diameter d	12.00 mm
Thread G1	G1/4"-M
Thread length LG1	7.6 mm
Key width SW1	17.0 mm

Design data STV-T G1/4-AG 12

Plug union, T

STV-T G1/4-AG 12



Art.-Nr.: 10.09.02.00045



Technical data

Attribute	Value
Weight	113.40 g
Material	Brass
Design hose type	12-9
Pressure range (operating pressure) [bar]	bar
Operating temperature	°C
Product family	STV



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.09.02.00045



Ordering Data Accessories 10.09.02.00045

Typ		Item number
Compressed-air hose	VSL 12-9 PE BL	10.07.09.00050
Vacuum hose (meter)	VSL 12-9 PU MI-TR	10.07.09.00037



WWW.SCHMALZ.COM/10.09.02.00045