


VTR G1/2-IG 5xG3/8 POM


Art.-Nr.: 10.09.03.00092

**Technical data**

Attribute	Value
Material	Polyoxymethylene
Length L	76.00 mm
Width B	55.00 mm
Height H	35.00 mm
Outlets	5 x thread G3/8"-F
Inlet	G1/2"-IG

VTR G1/2-IG 5xG3/8 POM

Vacuum / compressed air distributor VTR is delivered as a ready-to-connect product.



Design data VTR G1/2-IG 5xG3/8 POM

Design data

Attribute	Value
Length L2	38.00 mm
Length L	76.00 mm
Width B	55.00 mm
Height H	35.00 mm
Internal diameter d	6.50 mm
Thread G1	G1/2"-F
Thread length LG1	15.0 mm
Thread G2	G3/8"-F
Thread length LG2	14.0 mm
Hole spacing Y1	42.0 mm
Hole spacing Y2	27.0 mm
Hole spacing X1	30.2 mm
Distribution type	5 x thread G3/8"-F

Art.-Nr.: 10.09.03.00092

**Technical data**

Attribute	Value
Weight	154.00 g
Material	Polyoxymethylene
Product family	VTR
Tightening torque G1 (max.)	3.0 Nm
Tightening torque G2 (max.)	3.0 Nm

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.09.03.00092**Ordering Data Accessories 10.09.03.00092**

Typ		Item number
Hose sleeve	ST G1/2-AG 9 MS-V	10.08.03.00161
Hose sleeve	ST G1/2-AG 13 MS-V	10.08.03.00162
Hose sleeve	ST G1/2-AG 19 MS-V	10.08.03.00163
Hose sleeve	ST G3/8-AG 9 MS-V	10.08.03.00159
Hose sleeve	ST G3/8-AG 13 MS-V	10.08.03.00160
Sealing screw with collar	VRS-SB G3/8-AG ISKT O-Ring	10.08.06.00045
Sealing screw with collar	VRS-SB G1/2-AG ISKT O-Ring	10.08.06.00046

