

VTR G3/8-IG 9xG1/4 POM


Art.-Nr.: 10.09.03.00100

**Technical data**

Attribute	Value
Material	Polyoxymethylene
Length L	116.00 mm
Width B	39.00 mm
Height H	24.00 mm
Outlets	9 x thread G1/4"-F
Inlet	G3/8"-IG

VTR G3/8-IG 9xG1/4 POM

Vacuum / compressed air distributor VTR is delivered as a ready-to-connect product.



Design data VTR G3/8-IG 9xG1/4 POM

Design data

Attribute	Value
Length L2	58.00 mm
Length L	116.00 mm
Width B	39.00 mm
Height H	24.00 mm
Internal diameter d	6.50 mm
Thread G1	G3/8"-F
Thread length LG1	10.5 mm
Thread G2	G1/4"-F
Thread length LG2	10.5 mm
Hole spacing Y1	27.0 mm
Distribution type	9 x thread G1/4"-F

VTR G3/8-IG 9xG1/4 POM

Art.-Nr.: 10.09.03.00100

**Technical data**

Attribute	Value
Weight	110.00 g
Material	Polyoxymethylene
Product family	VTR
Tightening torque G1 (max.)	3.0 Nm
Tightening torque G2 (max.)	2.0 Nm

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.09.03.00100**Ordering Data Accessories 10.09.03.00100**

Typ		Item number
Sealing screw with collar	VRS-SB G1/4-AG ISKT O-Ring	10.08.06.00044
Sealing screw with collar	VRS-SB G3/8-AG ISKT O-Ring	10.08.06.00045
Plug union, straight	STV-GE G1/4-AG 10	10.08.02.00251
Plug union, straight	STV-GE G3/8-AG 10	10.08.02.00252
Plug union, straight	STV-GE G3/8-AG 8	10.08.02.00237
Plug union, straight	STV-GE G1/4-AG 8	10.08.02.00207
Plug union, straight	STV-GE G3/8-AG 12	10.08.02.00209

