

# Control Unit mGrip SRCU-Mini-A-UM



Art.-Nr.: 10.13.07.00161



## Technical data

Inputs / outputs	Analog
Weight	1,890.00 g
Voltage DC	24 V - DC
Pressure range (operating pressure) [bar]	5.9 ... 6.9 bar
Version	without mounting plate

SRCU-Mini-A-UM

The control module SRCU Mini can be delivered either assembled (M) or unassembled (UM). The control module SRCU Basic is delivered assembled.

## Design data

Design data SRCU-Mini-A-UM



## Technical data

Inputs / outputs	Analog
Weight	1,890.00 g
Voltage DC	24 V - DC
Pressure range (operating pressure) [bar]	5.9 ... 6.9 bar
Pressure max.	6.90 bar
Version	without mounting plate



[WWW.SCHMALZ.COM/10.13.07.00161](http://WWW.SCHMALZ.COM/10.13.07.00161)

Control Unit mGrip

# SRCU-Mini-A-UM



Art.-Nr.: 10.13.07.00161



## Ordering Data Accessories 10.13.07.00161

Typ		Item number
Vacuum hose (meter)	VSL 8-6 PU MI-TR	10.07.09.00003
Vacuum hose (meter)	VSL 10-7 PU MI-TR	10.07.09.00084
Compressed-air hose	VSL 8-6 PE BL	10.07.09.00015
Vacuum hose (meter)	VSL 10-7 PE MI-TR	10.07.09.00083
Compressed-air hose	VSL 12-9 PE BL	10.07.09.00050
Vacuum hose (meter)	VSL 12-9 PU MI-TR	10.07.09.00037



[WWW.SCHMALZ.COM/10.13.07.00161](http://WWW.SCHMALZ.COM/10.13.07.00161)