




### Technical data

Weight	2,812.51 g
Voltage DC	24 V - DC
Pressure range (operating pressure) [bar]	3.0 ... 6.0 bar
Length L	226.00 mm
Width B	164.00 mm
Height H	86.00 mm

### SRCU-Basic

The control module SRCU Mini can be delivered either assembled (M) or unassembled (UM). The control module SRCU Basic is delivered assembled.



### Design data

Length L1	226.00 mm
Length L	226.00 mm
Width B1	194.00 mm
Width B	164.00 mm
Height H1	92.80 mm
Height H	86.00 mm
Internal diameter d	5.50 mm
Hole spacing Y1	108.9 mm
Hole spacing X1	179.0 mm

### Design data SRCU-Basic



Control Unit mGrip  
**SRCU-Basic**



Art.-Nr.: 10.13.07.00400



**Technical data**

Weight	2,812.51 g
Voltage DC	24 V - DC
Pressure range (operating pressure) [bar]	3.0 ... 6.0 bar
Pressure max.	6.00 bar



**Ordering Data Accessories 10.13.07.00400**

Typ		Item number
Ejector tester	EJEK-TEST SMPi/SCPi	10.02.02.03588



[WWW.SCHMALZ.COM/10.13.07.00400](http://WWW.SCHMALZ.COM/10.13.07.00400)